



D Series

W



RW




Switching Operation

1 NC / 1 NO Contacts


Slow Action

604.1103.002
D-U1 W




Snap Action

604.1153.156
D-SU1 W




Slow Action

604.1118.229
D-U1Z RW




Snap Action

604.1168.162
D-SU1 RW



2 NC Contacts


604.1803.090
D-A2 W



-

-

604.1818.741
D-A2Z RW




-

-

2 NO Contacts


604.1803.046
D-E2 W



-

-

604.1818.052
D-E2 RW




-

-

1 NC / 1 NO Contacts Overlapping


604.1303.134
D-UV1Z W



-

-

604.1318.140
D-UV1Z RW



-

-

Replacement actuator:

Technical Information

	Slow Action	Snap Action
Maximum Switching Voltage	240V	240V
Max. Switching Amps (up to)*	10A	10A
B10d (up to)*	20 Million	20 Million
Mechanical Service Life (up to)*	10 x 10 ⁶	10 x 10 ⁶
Switching Frequency	≤ 100/min	≤ 100/min
Operating Temperature	-30 °C to +80 °C	-30 °C to +80 °C
Protection Rating	IP65	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	400VAC	400VAC

Approvals

* Depending on switching system - see technical information for details



Special features/variants (on request)

- Also available with following contacts:
3 NC contacts (larger enclosure)
3 NO contacts (larger enclosure)
2 NC / 2 NO contact (larger enclosure)

	Slow Action	Snap Action
Maximum Switching Voltage	240V	240V
Max. Switching Amps (up to)*	10A	10A
B10d (up to)*	20 Million	20 Million
Mechanical Service Life (up to)*	10 x 10 ⁶	10 x 10 ⁶
Switching Frequency	≤ 100/min	≤ 100/min
Operating Temperature	-30 °C to +80 °C	-30 °C to +80 °C
Protection Rating	IP65	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	400VAC	400VAC



Special features/variants (on request)

- Also available with following contacts:
3 NC contacts (larger enclosure)
3 NO contacts (larger enclosure)
2 NC / 2 NO contact (larger enclosure)

Drawing dimensions in mm