

STANDARD PLUGGABLE PRINTED CIRCUIT US Pin Spacing^a Screw-Cam Clamp Plug

For standard industrial plug-in applications where multiple wire-to-board connections must be made quickly and simultaneously.

Ideal for limited access application, wire entry and screws on the same side.

- Multipole, Single Mold Construction
- Industry Standard Compatible
- Optional Keying Prevents Misplugging
- Housing Material: Polyamide 6.6
- Standard Color: Green

^aBlocks with metric pin spacing begin on page 132.

Ratings
IEC/VDE
 (File No. E101811)
 (File No. LR68503)

Ordering Information

No. of Poles

Pin Header, US (Inch) Pole Spacing



AKZ1200

Wire Entry and Screws on Same Side and in Same Direction as Plug-In

Pole Spacing 5.08mm (.200)
Stripping Length 7mm (.276)
Screw Hole Diameter 3mm (.118)

Use with STLZ950, STLZ955, STLZ990, STLZ11, STLZ970, STLZ975 Headers

Wire Range	Current	Voltage
0.5-2.5mm ²	12A	250V
22-12 AWG	15A	300V
22-14 AWG	15A	300V

Type	Cat. No.	Length L mm (in.)	Std. Pk.
AKZ1200/2	36.102	10.16 (.40)	100
AKZ1200/3	36.103	15.24 (.60)	100
AKZ1200/4	36.104	20.32 (.80)	50
AKZ1200/5	36.105	25.40 (1.00)	50
AKZ1200/6	36.106	30.48 (1.20)	50
AKZ1200/7	36.107	35.56 (1.40)	30
AKZ1200/8	36.108	40.64 (1.60)	30
AKZ1200/9	36.109	45.72 (1.80)	30
AKZ1200/10	36.110	50.80 (2.00)	20
AKZ1200/11	36.111	55.88 (2.20)	20
AKZ1200/12	36.112	60.98 (2.40)	20
AKZ1200/13	36.113	66.04 (2.60)	20
AKZ1200/14	36.114	71.14 (2.80)	20
AKZ1200/15	36.115	76.20 (3.00)	20
AKZ1200/16	36.116	81.28 (3.20)	15
AKZ1200/17	36.117	86.36 (3.40)	15
AKZ1200/18	36.118	91.44 (3.60)	15
AKZ1200/19	36.119	96.52 (3.80)	15
AKZ1200/20	36.120	101.60 (4.00)	15
AKZ1200/21	36.121	106.66 (4.20)	10
AKZ1200/22	36.122	111.76 (4.40)	10
AKZ1200/23	36.123	116.84 (4.60)	10
AKZ1200/24	36.124	121.92 (4.80)	10

Dimensions			
mm	in.	mm	in.
2.70	0.106	15.00	0.591
5.08	0.200	27.50	1.083
8.30	0.327		

