









- NOTES:
- 1. MATERIAL: ABS
 - 2. FINISH: BODY/COVER - GRAY
 - 3. RoHS COMPLIANT
 - 4. CONTINUOUS GASKET IN COVER
 - 5. -20 °C TO +65 °C EXTENDED EXPOSURE CONDITION
 - 6. SUPPLIED WITH TWO M4 x 8mm LG. TRUSS HEAD MACHINE SCREWS
 - 7. DIMENSIONS ARE INCH [MM]
 - 8. OPTIONAL ACCESSORIES:
INTERNAL STEEL PANEL - #PTX-22510
INTERNAL PLASTIC PANEL - #PTX-22510-P
MOUNTING BRACKET KIT (STAINLESS STEEL) - #NBX-10920




OPTIONAL INTERNAL PANEL AND
SUGGESTED PC BOARD LAYOUT




SECTION A-A



INSIDE VIEW OF BASE



BOTTOM VIEW



DRAWING FOR REFERENCE
WE RESERVE THE RIGHT TO MAKE CHANGES TO OUR
STANDARD PRODUCTS. PLEASE CONSULT WITH BUD INDUSTRIES
PRIOR TO USING THIS DRAWING FOR DESIGN PURPOSE.