





SECTION A-A
SCALE 1 : 4



COVER NOT SHOWN
M5 THREADED INSERT X 4

LATCH X 2

HINGES X 2

NOTES:

- MATERIAL: BODY - POLYCARBONATE 10% FIBERGLASS REINFORCED
COVER - POLYCARBONATE
UL508 /NEMA TYPE 4X WITH IP-67 TUV RATING & UL-94V0 RATING
- FINISH: BODY - LIGHT GRAY
COVER - LIGHT GRAY OR CLEAR (-C)
- ALL HOLE DIAMETERS HAVE +/- .005(0.13) TOLERANCE
ALL OTHER DIMENSIONS HAVE +/- 0.03(0.76) TOLERANCE UNLESS OTHERWISE SPECIFIED
- CONTINUOUS GASKET IN COVER
- SUPPLIED WITH TWO M4 x 8mm LG. TRUSS HEAD MACHINE SCREWS
- DIMENSIONS ARE INCH [MM]
- DRAWING FOR REFERENCE
- OPTIONAL ACCESSORIES:
INTERNAL STEEL PANEL - #PTX-11070
INTERNAL PLASTIC PANEL - #PTX-11070-P
MOUNTING BRACKET KIT (STAINLESS STEEL) - #NBX-10922

DRAWING FOR REFERENCE

WE RESERVE THE RIGHT TO MAKE CHANGES TO OUR STANDARD PRODUCTS. PLEASE CONSULT WITH BUD INDUSTRIES PRIOR TO USING THIS DRAWING FOR DESIGN PURPOSE.