

ODU SPRINGTAC® , ODU LAMTAC®



ODU solid pin 3.0mm Ag solder-/screw termination M4



Part number	181.110.000.301.000
Category	Contact

Contact type	Pins
Contact diameter	3 mm
Termination type	Screw-solder

Material	Cu-alloy
----------	----------

Technical drawing of a bolt with the following dimensions and specifications:

- Thread: M4
- Head diameter: $\varnothing 2.3$
- Head height: 5
- Shank diameter: $\varnothing 3$
- Shank length: 14
- Total length: 15.5
- End diameter: $\varnothing 6$
- Tolerance diameter A: -0.03

[3D-File \(STP File\)](#)