

185.967.000.306.000

ODU AMC® Series T



specific crimp contacts

ODU specific crimp contacts for ODU AMC® Series T pin contact, #20MD, AWG 20-24 - For smaller termination cross section and higher contact density without BIN color code

Basic information

Part number	185.967.000.306.000
Category	Contact

Contact insert description

Contact type	Pins
Contact diameter	0.9 mm
Termination type	Crimp
Wire cross section AWG	AWG 20 – 24

Crimptools



080.000.072.000.000
Crimp tool

Tool	080.000.072.000.000
Tool Instruction	Crimp_Instruction_080.000.072.000.000_080.000.073.000.000.pdf
Tool Adjustment Dimension	1.1
Tool Positioner One	080.000.072.106.000

Removal tools

085.613.100.090.000

specific insertion & Removal tool

Mechanical and environmental data

Upper temperature limit	175 °C
Weight	0.1 g