



Basic information

Part number	209.745.004.037.000
Category	isulation_body
Size	3

Contact insert description

Number of contacts	37
Contact type	sockets
Contact diameter	1.5 mm

Mechanical and environmental data

Mating cycles	minimum 100.000
Max. operating temperature	120 °C
Min. operating temperature	-40 °C
Weight	60.01 g

Material and surface treatments

Material	pbt_fiber_glass_reinforced_acc_to_ul_94
----------	---

Further technical information and downloads

3D-File [STP File]
Assembly Instruction