

756.199.402.000.000

ODU MINI-MED®



ODU MINI-MED® Receptacle, IP67, 4 Contacts, 90° Key

ODU MINI-MED® Front panel mount receptacle, IP67, 4 Contacts, 90° Key



Basic information

Part number	756.199.402.000.000
Category	Connector

Contact insert description

Number of contacts	4
Contact type	Sockets
Contact diameter	0.7 mm
Termination type	Solder cup
Termination diameter	0.65 mm
Wire cross section AWG	AWG 26

Technical information

Max. current single contact	7 A
-----------------------------	-----

Mechanical and environmental data

Locking principle	Break-Away
Keying	Coding 90°
Mating cycles	1.000
Max. operating temperature	80 °C
Min. operating temperature	-15 °C
Weight	2.59 g

Material and surface treatments

Material	PA / TPU
Insulator material	PA
Contact material	Blank

Further technical information and downloads

[Catalogue](#)