

756.199.403.000.000

ODU MINI-MED®



ODU MINI-MED® Receptacle, IP67, 3 Contacts, 90° Key

ODU MINI-MED® Front panel mount receptacle, IP67, 3 Contacts, 90° Key



Basic information

Part number	756.199.403.000.000
Category	Connector

Contact insert description

Number of contacts	3
Contact type	Sockets
Contact diameter	0.9 mm
Termination type	Solder cup
Termination diameter	0.85 mm
Wire cross section AWG	AWG 22

Technical information

Max. current single contact	7.5 A
-----------------------------	-------

Mechanical and environmental data

Locking principle	Break-Away
Keying	Coding 90°
Mating cycles	1.000
Max. operating temperature	80 °C
Min. operating temperature	-15 °C
Weight	2.58 g

Material and surface treatments

Material	PA / TPU
Insulator material	PA
Contact material	Blank

Further technical information and downloads

[Catalogue](#)