

923.000.005.000.429

ODU AMC® Series T



MIL specification crimp

MIL specification crimp contacts for ODU AMC® Series T pin contact, #22D, AWG 20-24 / BIN color: orange, blue, black [MIL-Part No.: M39029/58-360]



Basic information

Part number	923.000.005.000.429
Category	Contact

Contact insert description

Contact type	Pins
Contact diameter	0.76 mm
Termination type	Crimp
Wire cross section AWG	AWG 22 – 26

Crimptools



080.000.072.000.000

Crimp tool

Tool	080.000.072.000.000
Tool Instruction	Crimp_Instruction_080.000.072.000.000_080.000.073.000.000.pdf
Tool Adjustment Dimension	1.1
Tool Positioner One	080.000.072.101.000

Removal tools



085.613.100.060.000

MIL standard plastic too



085.613.100.030.000

MIL standard metal tweezers

Mechanical and environmental data

Upper temperature limit	175 °C
Weight	0.08 g

Material and surface treatments

Material	Cu-alloy
Color option (Front or back nut)	Black