


straight_break_away_plug_for_bend_relief

size: 3, IP6K8 / IP6K9K, keying: a, number_of_contacts: 4, solder_cup, contact_type: pins, Signal



Basic information

Part number	A13YAR-P04XTS0-0000
Category	connector
Type of connector	plug
Assembly situation	straight
Size	4e0740

Contact insert description

Transmission type	Signal
Number of contacts	4
Contact type	pins
Contact diameter	f96cd4
Termination type	solder_cup
Termination diameter	68d6e9
Wire cross section AWG	3fd1bd

Technical information

Max. current single contact	7a5ea0	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	22	VDE 0298-4:2003
Test voltage	1.65 kV AC	EIA-364-20F:2019-02

Cable description

Cable outlet	overmolding
Min. cable diameter	6
Max. cable diameter	11.5

Mechanical and environmental data


Locking principle	break_away
Keying	a
Mating cycles	0f8eb4
IP class	IP6K8 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Weight	15.6 g

ip_protection_class_refers_to_mated_condition


Material and surface treatments

Material	aluminum_with_ruthenium_finish
Insulator material	peek
Contact material	gold


DIMENSIONS:



CODING:A



POSITIONS: 4 Positions



Further technical information and downloads

[Assembly Instruction](#)