

straight_break_away_plug_for_bend_relief

size: 1.5, IP6K8 / IP6K9K, keying: c, number_of_contacts: 19, solder_cup, contact_type: flat_contact, Signal



Basic information

Part number	A1AYCR-P19WDD0-R000
Category	connector
Type of connector	plug
Assembly situation	straight
Size	9f29a1

Contact insert description

Transmission type	Signal
Number of contacts	19
Contact type	flat_contact
Contact diameter	e40347
Termination type	solder_cup
Termination diameter	1d7c76
Wire cross section AWG	562f2b

Technical information

Max. current single contact	3a6630	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	0.9	VDE 0298-4:2003
Test voltage	0.6 kV AC	EIA-364-20F:2019-02

Cable description

Cable outlet	overmolding
Min. cable diameter	3.2
Max. cable diameter	8

Mechanical and environmental data


Locking principle	break_away
Keying	c
Mating cycles	9e1839
IP class	IP6K8 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Weight	8.33 g

ip_protection_class_refers_to_mated_condition


Material and surface treatments

Material	cu_alloy_with_ruthenium_finish
Contact material	gold


DIMENSIONS:



CODING:C



POSITIONS: 19 positions



Further technical information and downloads

[3D-File \[STP File\]](#)

[Assembly Instruction](#)