

C10WBM-PD1XMM0-0000

odu_amc®_hd



straight_screw_lock_plug_for_bend_relief

size_0_ip6k8_ip6k9k_coding_b_red_12_contacts_pins_solder_cup_data_transmission

	Basic information	
	Part number	C10WBM-PD1XMM0-0000
	Category	connector
	Type of connector	plug
Assembly situation		straight

Contact insert description

Special features	data_transmission
Transmission type	USB® 3.2 Gen 1x1 (5 Gbit/s)
Number of contacts	12
Contact type	pins
Contact diameter	0.3 mm; 0.7 mm
Termination type	solder_cup
Termination diameter	0.85 mm
Wire cross section AWG	AWG 28; AWG 22

Technical information

Max. current single contact	1 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Test voltage	0.75 kV DC	EIA-364-20F:2019-02

Cable description

Cable outlet	overmolding
Min. cable diameter	3.2
Max. cable diameter	7

Mechanical and environmental data


Locking principle	screw_lock
Keying	b
Mating cycles	5.000
IP class	IP68 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Weight	10.1 g

ip_protection_class_refers_to_mated_condition


Material and surface treatments

Material	cu_alloy_(blank)
Contact material	gold

DIMENSIONS:



CODING: B



Further technical information and downloads

Connection diagram

connection_diagram_D1_pin_usb_3_2_gen1x1_pin_typ_a

[3D-File \(STP File\)](#)

[Assembly Instruction](#)

[Technical specifications](#)