

receptacle_with_break_away_locking_for_rear_panel_mounting_with_cable_outlet

size_0_ip6k8_ip6k9k_coding_a_light_brown_7_contacts_sockets_solder_cup_signal_transmission



Basic information

Part number	G60WAM-P07WFG0-0000
Category	connector
Type of connector	receptacle
Assembly situation	rear_panel_mounting
Size	5feceb

Contact insert description

Transmission type	Signal
Number of contacts	7
Contact type	sockets
Contact diameter	ec72e6
Termination type	solder_cup
Termination diameter	08561d
Wire cross section AWG	374cb3

Technical information

Max. current single contact	2f071a	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	3.25 A	VDE 0298-4:2013
Test voltage	0.75 kV DC	EIA-364-20F:2019-02

Cable description

Cable outlet	overmolding
Min. cable diameter	3.2
Max. cable diameter	7




Mechanical and environmental data

Locking principle	break_away
Keying	a
Mating cycles	9e1839
IP class	IP68 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Tightening torque	1 Nm
Weight	8 g

ip_protection_class_refers_to_mated_condition

Material and surface treatments

Material	cu_alloy_with_ruthenium_finish
Contact material	gold



Further technical information and downloads

[3D-File \(STP File\)](#)

[Assembly Instruction](#)

[Technical specifications](#)