

GCOWBM-P09UM00-000L

odu_amc®_hd



receptacle_with_screw_lock_for_rear_panel_mounting

size_0_ip6k8_ip6k9k_coding_b_red_9_contacts_sockets_pcb_data_transmission_and_high_power_usb®_2.0_480_mbits+_power



Basic information

Part number	GCOWBM-P09UM00-000L
Category	connector
Type of connector	receptacle
Assembly situation	rear_panel_mounting

Contact insert description

Special features	data_transmission
Transmission type	USB® 2.0 (480 Mbit/s) + Power
Number of contacts	9
Contact type	sockets
Contact diameter	0.3 mm; 0.7 mm
Termination type	pcb
Termination diameter	0.3 mm

Technical information

Max. current single contact	1 A; 5 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Test voltage	0.75 kV DC	EIA-364-20F:2019-02

Mechanical and environmental data


Locking principle	screw_lock
Keying	b
Mating cycles	5.000
IP class	IP68 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Tightening torque	1 Nm
Weight	5.78 g

ip_protection_class_refers_to_mated_condition


Material and surface treatments

Material	cu_alloy_with_ruthenium_finish
Contact material	gold


DIMENSIONS:




CODING: B




POSITIONS: 9 positions



PCB-LAYOUT:



PANEL CUT OUT:



Further technical information and downloads

Connection diagram	con_usb_2_power
--------------------	-----------------

[3D-File \(STP File\)](#)

Technical specifications
--