

**Not available anymore - alternative: G4 in size 1****Basic information**

|             |                     |
|-------------|---------------------|
| Part number | GE1MC7-P05LJG0-0000 |
| Category    | Connector           |

**Contact insert description**

|                      |            |
|----------------------|------------|
| Number of contacts   | 5          |
| Contact type         | Sockets    |
| Termination type     | Solder cup |
| Termination diameter | 0.85 mm    |

**Technical information**

|                             |       |
|-----------------------------|-------|
| Max. current single contact | 7.5 A |
|-----------------------------|-------|

**Mechanical and environmental data**

|                            |            |
|----------------------------|------------|
| Keying                     | Coding 60° |
| Mating cycles              | 5.000      |
| Max. operating temperature | 120 °C     |
| Min. operating temperature | -50 °C     |
| Weight                     | 6 g        |

**Material and surface treatments**

|                    |      |
|--------------------|------|
| Insulator material | PEEK |
| Contact material   | Gold |

**Further technical information and downloads**[3D-File \[STP File\]](#)