

Not available anymore - alternative: G4 in size 1

Basic information

Part number	GE1MC7-P10LCC0-0000
Category	Connector

Contact insert description

Number of contacts	10
Contact type	Sockets
Termination type	Solder cup
Termination diameter	0.45 mm

Technical information

Max. current single contact	4 A
-----------------------------	-----

Mechanical and environmental data

Keying	Coding 60°
Mating cycles	5.000
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	9.999 g

Material and surface treatments

Insulator material	PEEK
Contact material	Gold

Further technical information and downloads

[3D-File \[STP File\]](#)