

receptacle_with_break_away_locking_for_rear_panel_mounting

size: 1.5, IP6K8 / IP6K9K, keying: a, number_of_contacts: 19, pcb, contact_type: pogo_pins, Signal



Basic information

Part number	GKAYAR-P19VD00-R00L
Category	connector
Type of connector	receptacle
Assembly situation	rear_panel_mounting
Size	9f29a1

Contact insert description

Transmission type	Signal
Number of contacts	19
Contact type	pogo_pins
Contact diameter	e40347
Termination type	pcb
Termination diameter	88d6d3

Technical information

Max. current single contact	3a6630	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	0.9	VDE 0298-4:2003
Test voltage	0.6 kV AC	EIA-364-20F:2019-02

Mechanical and environmental data


Locking principle	break_away
Keying	a
Mating cycles	9e1839
IP class	IP6K8 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Tightening torque	3 Nm
Weight	6.83 g

ip_protection_class_refers_to_mated_condition


Material and surface treatments

Material	cu_alloy_with_ruthenium_finish
Contact material	gold


CODING:A



POSITIONS: 19 positions



PANEL CUT OUT:



Further technical information and downloads

[3D-File \(STP File\)](#)

[Assembly Instruction](#)