

straight_push_pull_plug_for_bend_relief

size: 2, IP6K8 / IP6K9K, keying: a, number_of_contacts: 6, solder_cup, contact_type: pins, Signal



Basic information

Part number	S12YAR-P06XPH0-0000
Category	connector
Type of connector	plug
Assembly situation	straight
Size	d4735e

Contact insert description

Transmission type	Signal
Number of contacts	6
Contact type	pins
Contact diameter	513afe
Termination type	solder_cup
Termination diameter	47dc8e
Wire cross section AWG	e0cfa8

Technical information

Max. current single contact	3a9ebe	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	10.5	VDE 0298-4:2003
Test voltage	800 V	EIA-364-20F:2019-02

Cable description

Cable outlet	overmolding
Min. cable diameter	5
Max. cable diameter	10

Mechanical and environmental data


Locking principle	push_pull
Keying	a
Mating cycles	0f8eb4
IP class	IP6K8 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Weight	12.31 g

ip_protection_class_refers_to_mated_condition


Material and surface treatments

Material	aluminum_with_ruthenium_finish
Insulator material	peek
Contact material	gold


DIMENSIONS:



CODING:A



POSITIONS: 6 positions



Further technical information and downloads

[Assembly Instruction](#)