

specific crimp contacts

ODU specific crimp contacts for ODU AMC® Series T pin contact, #20MD, AWG 20-24 - For smaller termination cross section and higher contact density without BIN color code

Basic information

Part number	185.967.000.306.000
Category	Contact
Size	#20MD

Contact insert description

Contact type	Pins
Contact diameter	0.9 mm
Termination type	Crimp
Wire cross section AWG	AWG 20 – 24

Crimptools



080.000.072.000.000
Crimp tool

Part number	185.967.000.306.000
Tool	080.000.072.000.000
Tool Instruction	odu-crimp-instruction-080.000.072.000.000-de-en [1].pdf
Tool Adjustment Dimension	1.1
Tool Positioner One	080.000.072.106.000

Removal tools

085.613.100.090.000

specific insertion & Removal tool

Mechanical and environmental data

Upper temperature limit	175 °C
Weight	0.1 g