

923.000.005.000.299

ODU AMC® Series T



MIL specification crimp

MIL specification crimp contacts for ODU AMC® Series T socket contact, #16, AWG 16-20 / BIN color: orange, green, gray [MIL-Part No.: M39029/57-358]

		Basic information	
Part number	923.000.005.000.299	Category	Contact
Size	#16		

Contact insert description

Contact type	Sockets
Contact diameter	1.6 mm
Termination type	Crimp
Wire cross section AWG	AWG 16 – 20

Crimptools



080.000.073.000.000

Crimp tool

Part number	923.000.005.000.299
Tool	080.000.073.000.000
Tool Instruction	odu-crimp-instruction-080.000.073.000.000-de-en (1).pdf
Tool Adjustment Dimension	1.1
Tool Positioner One	080.000.073.101.000

Removal tools



085.613.100.020.000

MIL standard plastic too



085.613.100.070.000

MIL standard metal tweezers



085.613.100.070.001

MIL standard metal tweezers

Cable description

Cable diameter	16
----------------	----

Mechanical and environmental data

Upper temperature limit	200 °C
Weight	0.4 g

Material and surface treatments

Material	CuBe-alloy
Color option (Front or back nut)	Gray