

923.000.005.000.427

ODU AMC® Series T



MIL specification crimp

MIL specification crimp contacts for ODU AMC® Series T pin contact, #16, AWG 16-20 / BIN color: orange, blue, yellow [MIL-Part No.: M39029/58-364]



Basic information

Part number	923.000.005.000.427
Category	Contact
Size	#16

Contact insert description

Contact type	Pins
Contact diameter	1.6 mm
Termination type	Crimp
Wire cross section AWG	AWG 16 – 20

Crimptools



080.000.073.000.000

Crimp tool

Part number	923.000.005.000.427
Tool	080.000.073.000.000
Tool Instruction	odu-crimp-instruction-080.000.073.000.000-de-en (1).pdf
Tool Adjustment Dimension	1.1
Tool Positioner One	080.000.073.101.000

Removal tools



085.613.100.020.000

MIL standard plastic too



085.613.100.070.000

MIL standard metal tweezers



085.613.100.070.001

MIL standard metal tweezers

Cable description

Cable diameter	16
----------------	----

Mechanical and environmental data

Upper temperature limit	200 °C
Weight	0.32 g