

Not available anymore - alternative: G4 in size 1**Basic information**

Part number	GE1M07-P02LPH0-0000
Category	Connector

Contact insert description

Number of contacts	2
Contact type	Sockets
Contact diameter	1.3 mm
Termination type	Solder cup
Termination diameter	1.1 mm

Technical information

Nominal current single contact	12 A
--------------------------------	------

Mechanical and environmental data

Mating cycles	5.000
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	5.92 g

Material and surface treatments

Insulator material	PEEK
Contact material	Cu-alloy with gold finish

Further technical information and downloads[3D-File \[STP File\]](#)