

Not available anymore - alternative: G4 in size 1**Basic information**

Part number	GE1MA7-P07LFG0-0000
Category	Connector

Contact insert description

Number of contacts	7
Contact type	Sockets
Contact diameter	0.7 mm
Termination type	Solder cup
Termination diameter	0.85 mm

Technical information

Nominal current single contact	7.5 A
--------------------------------	-------

Mechanical and environmental data

Keying	Coding 40°
Mating cycles	2.000
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	6 g

Material and surface treatments

Insulator material	PEEK
Contact material	Cu-alloy with gold finish

Further technical information and downloads[3D-File \[STP File\]](#)