

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

(C) COPYRIGHT 20

ALL RIGHTS RESERVED.



LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECR-17-000969	20DEC2016	X.X	X.X
	D	ECR-18-018978	15FEB2019	F.F	M.S
	E	ECR-19-010701	16AUG2019	M.S	M.S
	EI	ECR-19-013399	26DEC2019	F.F	M.S


26.20



SCALE 4:1



Ø 4.50±0.20 (2X)



PART NUMBER	PART COLOR
2834036-1	ORANGE

NOTES:

1. TE PART NUMBER: SEE TABLE.
2. MATERIAL: COPPER ALLOY.
3. HOUSING: NYLON, UL 94-V0, COLOR: ORANGE.
4. FINISH: TIN PLATING OVERALL.
5. APPLICABLE MATING RECEPTACLE: 2834037 SERIES.
6. APPLICABLE WIRE: 18-22 AWG SOLID.
7. STRIP LENGTH: 9.0-9.5mm.
8. PRODUCT COMPLIES TO UL 2459 REQUIREMENT AND QUALIFIED: ZMNA.E308110; ZMNA7.E208110.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	±0.5
0-PLC	±10
1-PLC	±10
2-PLC	±5.0
3-PLC	±5.0
4-PLC	±5.0
ANGLES	±5°
MATERIAL	FINISH

DWN	26DEC2019
CHK	FRANK FAN
APVD	GEORGE FU
PRODUCT SPEC	MING SHI
APPLICATION SPEC	
WEIGHT	-
CUSTOMER DRAWING	

TE Connectivity	
NAME	
PLUG	
2 PIN WIRE TO WIRE CONNECTOR	
SIZE	CAGE CODE
DRAWING NO	RESTRICTED TO
A300779	C-2834036
SCALE 4:1	SHEET 1 OF 2
REV E1	

