


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-009839	07-07-14	DM	DM



- 4. PART NO. DRC70-GKT-AD
- 3. THICKNESS: 3.18 [.125]
- 2. TEMPERATURE RATING: -57°C TO +107°C [-70°F TO +225°F]
- 1. THIS PART IS USED ON
DRC12-70PX(E)-XXXX RECEPTACLE
WHERE X=A,B,C,D KEYS AND XXXX=MODIFICATION

2014

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2014 BY TE CONNECTIVITY

DIMENSIONS: MM [INCH]	DWN	D. MEYER 07JUL2014	MATERIAL	CLD CELL SPONGE	FINISH	BLACK	
	CHK	D. HASIBUAN 07JUL2014	TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	D. MEYER 07JUL2014					NAME
0 PLC ±	PRODUCT SPEC		GASKET, ADHESIVE, RECEPTACLE, 70PIN				
1 PLC ±	APPLICATION SPEC		DRC SERIES				
2 PLC ± 0.63 [.025]	SIZE	A 4	CAGE CODE	4AFU8	DRAWING NO	RESTRICTED TO	
3 PLC ±	WEIGHT	.907 G	C = DRC70-GKT-AD			-	
4 PLC ±	Customer Drawing					SCALE	NONE
ANGLES ± 5°						SHEET	1 OF 1
						REV	A