


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-012864	08-27-14	DM	DM



4. THICKNESS: 3.18 [.125]

3. PART NO. HD10-9-GKT-AD

2. TEMPERATURE RATING: -57°C TO +107°C [-70°F TO +225°F]


1. THIS PART IS USED ON HD10-9-XXX RECEPTACLES, WHERE XXX IS PIN ARRANGEMENTS. SEE INDIVIDUAL CUSTOMER DRAWINGS

DIMENSIONS:

MM [INCH]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	± 0.76 [.030]
3 PLC	±
4 PLC	±
ANGLES	± 5°



DWN D. MEYER 27AUG2014

CHK I. GRANTCHAROVA 27AUG2014

APVD D. MEYER 27AUG2014

PRODUCT SPEC

APPLICATION SPEC

WEIGHT .91 g

MATERIAL CLD CELL SPONGE

FINISH BLACK



TE Connectivity

NAME GASKET, ADHESIVE, RECEPTACLE, SIZE 9
HD10 SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A 4	4AFU8	C - HD10-9-GKT-AD	-

Customer Drawing

SCALE NONE

SHEET 1 OF 1

REV A

2014

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2014 BY TE CONNECTIVITY

THIS DRAWING IS UNPUBLISHED.