



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-013597	09-05-14	DM	DM




SECTION A-A



Backshell

Compression Nut

6. PART NO. M902-2344
5. CABLE STRIPPED LENGTH: 63.50 [2.500] MAX.
4. CABLE SIZE: Ø.570 - Ø.710
3. TEMPERATURE RATING: -40°C TO +134°C [-40°F TO +273°F]
2. THIS PART IS USED WITH:
COMPRESSION NUT, M902-2054
1. THIS PART IS USED ON
HD34-24-XXX-072 RECEPTACLES
HD36-24-XXX-072 PLUGS
SEE INDIVIDUAL CUSTOMER DRAWINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MEYER 05SEP2014		 TE Connectivity									
		CHK I. GRANTCHAROVA 05SEP2014											
DIMENSIONS: MM [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± .63 [.025] 3 PLC ± 4 PLC ± ANGLES ± 5°		NAME BACKSHELL, SIZE 24 -072 MOD CABLE SIZE: Ø.570 - Ø.710 HD30 SERIES									
													
MATERIAL PC/PBT		FINISH BLACK		APVD D. MEYER 05SEP2014		SIZE A3		CAGE CODE 4AFU8		DRAWING NO C M902-2344		RESTRICTED TO -	
				PRODUCT SPEC									
				APPLICATION SPEC									
				WEIGHT 18.64 g									
Customer Drawing						SCALE NONE		SHEET 1 OF 1		REV A			