

W28-XTBA-6

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield W28

TE Internal #: 5-1393250-7

Thermal Circuit Breaker, Series Trip, Black Actuator, 250 VAC, 32 VDC, 6 A, 1 Pole, 2.2 – 15 seconds Trip Time at 200%, Potter & Brumfield W28

[View on TE.com >](#)



Relays & Contactors > Circuit Breakers



Circuit Breaker Type: **Thermal**

Circuit Function: **Series Trip**

Illuminated: **Without**

Actuator Color: **Black**

Operating Voltage: **250 VAC**

Features

Product Type Features

Circuit Breaker Style	Fuse Holder Type
Illumination Type	No Light
Actuator Type	Push to Reset
Circuit Breaker Type	Thermal
Illuminated	Without

Configuration Features

Circuit Function	Series Trip
Number of Poles	1

Electrical Characteristics

Operating Voltage	32 VDC
Current Rating	6 A
Interrupt Capacity	1000A @ 250VAC/32VDC

Body Features

Bezel Color	Black
Actuator Color	Black

Contact Features

Trip Time at 200%	2.2 – 15 seconds
-------------------	------------------

Termination Features



Terminal Configuration	6.35 [.25] Straight Quick Connect Tab
------------------------	---------------------------------------

Mechanical Attachment

Mounting Options	Snap-In Panel Mount
Mounting Bushing	None

Dimensions

Panel Thickness (Recommended)	1.91 – 2.67 mm[.075 – .105 in]
-------------------------------	--------------------------------

Identification Marking

Stamped Marking Type	White Reset Marking
----------------------	---------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cadmium oxide (7.95% in Component) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

W28-XTBA-6

Thermal Circuit Breaker, Series Trip, Black Actuator, 250 VAC, 32 VDC, 6 A, 1 Pole, 2.2
– 15 seconds Trip Time at 200%, Potter & Brumfield W28



TE Part # 175022-1
250 PL EX REC. 18-14AWG PTBR

Also in the Series | Potter & Brumfield W28

Circuit Breakers(42)

Customers Also Bought

TE Part #L9000279-01
SMA Jack 50 Ohm .062 PCB Edge Mount

TE Part #524226-E
SRCA 6,20 2 M * SMD 137 E-HD 197 *
* * J

TE Part #3-1625963-9
HSA5 5R0 1%

TE Part #7-1625963-8
HSA5 2R2 5%

TE Part #1-1676814-4
HSA5 8R25 1%

TE Part #3-2176305-1
RP 1E 0.1W 221R 0.1% 25PPM 5K RL

TE Part #9-2176452-7
CPF 0201 5K36 0.1% 25ppm 1K RL

TE Part #5536406-5
ASSY,PIN,EUROCARD,"C",LEAD-FREE,A&C,64/9

TE Part #5650956-5
ASSEMBLY,RECEPTACLE,EURO,TYPE

TE Part #524191-E
SRCBUG A 6,20 * 2 CSI 206 E-HD
ADVCBK TR



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1393250-7_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1393250-7_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1393250-7_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

W28 Push to Reset Fuseholder-Type Thermal Circuit Breaker

English

Agency Approvals

VDE Certificate

English