



HM

TE Internal #: D34032-000

Metalized Silver, Industrial Label, Die-Cut, High Tack Acrylic Adhesive, 25.4 mm [1 in] Width, 12.7 mm [.5 in] Height, Polyester, HM, Standard Labels

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > HM High Tack Metalized Polyester Labels



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Acrylic Adhesive**

Compatible With Agency/Standards Products: **UL**

Product Width: **25.4 mm [1 in]**

[All HM High Tack Metalized Polyester Labels \(35\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	Metalized Silver
Primary Product Material	Polyester

Dimensions

Product Width	25.4 mm[1 in]
Product Height	12.7 mm[.5 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	3
Label Style	Die-Cut
Length of Label Roll	56.33 m[184.8 ft]
Label Thickness	97 Micron

Industry Standards

--	--



Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Method	Roll
Packaging Quantity	10000

Other

Label Adhesive Type	High Tack Acrylic Adhesive
---------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

HM-254127-10-8A

Metalized Silver, Industrial Label, Die-Cut, High Tack Acrylic Adhesive, 25.4 mm [1 in] Width, 12.7 mm [.5 in] Height, Polyester, HM, Standard Labels



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER




TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series | HM



Standard Labels(2)

Customers Also Bought




TE Part #097370-000
TTVF200YW-100




TE Part #354094-E
SMCB 16 M AB VV 7-03 CL * 0007 137 E004



TE Part #ZPF000000000011514
BJE 130



TE Part #104128-4
020 LOPRO HDR SP 30DP LATCH




TE Part #1055689-1
2367 5002 54,VERT PLUG




TE Part #6-1617772-1
FCB-205-AZ3=RELAY



TE Part #5-1814400-2
SMA R/A PCB Skt GZD



TE Part #2226910-1
NETT WARRIOR PLUG ASSEMBLY



TE Part #2-5174225-5
AMPLIMITE 050-2B HOR 68P M2.5



TE Part #2015357-4
C/A, UMCC/UMCC, 1.37 OD CABLE, 200MM LON



Documents

Product Drawings

HM-254127-10-8A

English

Datasheets & Catalog Pages

HM High Tack Metalized Polyester labels

English

IDENTIFICATION SELECTION GUIDE

English

Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English