

WX2020 Kit 120V



Item No: WX2020N

2-Channel Soldering Station, 200 W
(255 W)

KEY FEATURES

- + Power unit WX 2, with 2 channels, 2 soldering irons WXP 120 and 2 safety rests WSR 201
- + Simultaneous operation of 2 soldering tools

TECHNICAL DATA

Length	6.8 in
Dimensions L x W x H	174.0 x 154.0 x 135.0mm
Automatic Tool Identification	Yes
Benchtop Controller	Yes
Equipotential Bonding Socket	Via 3.5mm pawl socket on back of device
ESD Safe	Yes
Fuse	T2A
Interface	1x USB, 2x RS232, 1x Switching Output
Multilingual Display	Yes
Number of Channels	2
Power	200 W (255 W)
Temperature Accuracy °C	± 9°C
Temperature Accuracy °F	± 17°F
Temperature Range (Depends on Tool)	Adjustable from 100°C - 550°C (200°F - 999°F) Adjustable temperature range varies among tools
Temperature Range °C	100 - 450 °C
Temperature Range °F	200 - 850 °F
Temperature Stability °C	± 2°C
Temperature Stability °F	± 4°F
Tip Type	WX WXMT-MS XTB
Traceability	Yes
UPC	037103304803
USB	USB interface of firmware updates, parameterization and monitoring USB interface supports all standard USB flash drive types
Voltage	120V
Weight (Catalog)	3.45 kg
Product Family	WX Line Soldering Stations