

170MVNBK

Item No: 170MVNBK

General Purpose Shear Cutter

Weller® Xcelite® Micro Series General Purpose Shear Cutter are precision-engineered for electronics assembly.



KEY FEATURES

- + Superior blade by-pass shear cutting action
- + Better cuts with lower effort
- + Full-flush cuts soft wire up to 20 AWG (0.8 mm)
- + Highest quality carbon steel
- + Non-glare black finish
- + Lightweight construction
- + ESD-safe

TECHNICAL DATA

Length	127,0 mm, 5 in
Cutting Edge Length	8,7 mm, 11/32 in
ESD Safe	Yes
Handle Color	Blue
Head Length	19,1 mm, 3/4 in
Head Style	Full-flush
Head Width	12,7 mm, 1/2 in
Packaging	Boxed
Quantity Per Package	1
Tip Size	2,0 mm, 5/64 in
UPC	037103380814
Cuts Material Types	Soft Wire
Package Gross Weight	7.937 lb
Package Height	7.677 in
Package Length	15.354 in
Package Width	6.496 in
Case Pack Qty.	1
Product Family	Micro Series