



TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.25
.XX	±0.13
.XXX	±0.05

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER
ORIGINAL (1)




NOTES:

MATERIAL:

HOUSING: THERMOPLASTIC POLYESTER, UL94V-0

SHELL: STEEL, Sn or Ni PLATED

CONTACT: COPPER ALLOY SEE ORDERING GUIDE FOR PLATING



OPERATING TEMPERATURE: -55°C ~ 125°C


SIGNAL CONTACT CURRENT RATING: 5A PER CONTACT

SIGNAL CONTACT RESISTANCE: 10mΩ MAX.

INSULATOR RESISTANCE: 5000MΩ min.

DIELECTRIC

WITHSTANDING VOLTAGE: 1000V AC rms



COMBINATION D-SUB	SW REFERENCE NO.: 627 COMBO ASSEMBLY	
	DRAWN: C.B	DATE: JAN. 01/2019
CHECKED:		DATE:
SCALE: (IN C.A.D. 1:1)	SHEET 1 OF 4	
DRAWING NUMBER: 627-5W5-224-7N5	ISSUE 1	
PART NUMBER: 627-5W5-224-7N5		



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCE.



EDAC INC
TORONTO, ONTARIO
CANADA

YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	± 0.25
.XX	± 0.13
.XXX	± 0.05

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER
ORIGINAL

1



2W2



2WK2




5W1




3W3



3WK3



7W2



11W1



5W5



9W4



13W3




17W2



21W1




13W6




17W5




8W8




25W3




27W2




21W4




24W7



36W4



43W2



47W1

COMBINATION D-SUB	SW REFERENCE NO.: 627 COMBO ASSEMBLY	
	DRAWN: C.B	DATE: JAN. 01/2019
CHECKED:	DATE:	
SCALE: N.T.S	SHEET 2 OF 6	
DRAWING NUMBER: 627-5W5-224-7N5	ISSUE 1	
PART NUMBER: 627-5W5-224-7N5		




THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCE.




EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.


2W2 / 2WK2




3W3 / 3WK3




5W1 Male/Female




5W5 Male




8W8 Male




7W2 Male/Female




5W5 Female



8W8 Female




11W1 Male/Female




CURRENT RATING / ϕ A

- 10A / 2.2
- 20A / 3.3
- 30A / 3.7
- 40A / 4.2


17W2 Male/Female




24W7 Male/Female




21W4 Male/Female



27W2 Male/Female



21W1 Male/Female



COMBINATION D-SUB	SW REFERENCE NO.: 627 COMBO ASSEMBLY	
	DRAWN: C.B	DATE: JAN. 01/2019
	CHECKED:	DATE:
	SCALE: N.T.S	SHEET 3 OF 4
DRAWING NUMBER: 627-5W5-224-7N5	ISSUE 1	1
PART NUMBER: 627-5W5-224-7N5		



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCE.



EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	± 0.25
.XX	± 0.13
.XXX	± 0.05

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER

ORIGINAL

1

