


TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	1



SPECIFICATION:

ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V
 RATED CURRENT (PER CONTACT): 2A
 INSULATION RESISTANCE: 100MEGAOHMS MINIMUM
 DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60HZ
 CONTACT RESISTANCE: 30mOHMS MAXIMUM BEFORE TEST AND 60mOHMS MAXIMUM AFTER TEST AT POGO PIN WORKING STROKE

RECOMMENDED WORKING STROKE & FORCE:

STROKE 1.1mm (PER CONTACT): 80gf±20gf
 MECHANICAL LIFE: 10,000 CYCLES MIN.
 WORKING TEMPERATURE RANGE: -30~+85°C

MAGNETIC SPRING LOADED CONNECTOR, 4POS, FEMALE



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 688A04210A01E06		UNIT: MM
DRAWN: J.L.	DATE: 4/27/2023	
CHECKED: R.S.M	DATE: 4/27/2023	
SCALE: (IN CAD 1:1)	SHEET 1 OF 1	
DRAWING NUMBER: 688A04210A01E06		ISSUE 1
PART NUMBER: 688A04210A01E06		



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.