





REVISIONS			
REV.	DESCRIPTION	DATE	BY
1	ORIGINAL	DRAWN DATE	V.K
2	0.7 WAS 0.75, 12.3 WAS 12.4, 0.64 WAS 0.6, 2.4 WAS 2.5, 2.0 WAS 1.8, 1.7 WAS 1.8, 1.85 WAS 1.80, 2.0 WAS 1.8	05/26/2026	J.S.M



SECTION A-A
SCALE 6 : 1



SECTION B-B
SCALE 6 : 1



SECTION C-C
SCALE 6 : 1

SPECIFICATIONS
 VOLTAGE RATING: 250V AC/DC
 CURRENT RATING: 3A AC/DC
 WITHSTANDING VOLTAGE: 1000VAC/MINUTE
 TEMPERATURE RANGE: -40 °C TO 105 °C
 INSULATION RESISTANCE: 1000MΩ MIN.
 CONTACT RESISTANCE: 20mΩ MAX.
 INSULATION OD: 1.30MM (MAX.)

MATERIAL PHOSPOR BRONZE
 PLATING: TIN-PLATED
 WIRE RANGE: 24-30 AWG

USE WITH HOUSING: 14K-5XX-210-AA1
 MATES WITH CONTACT: 14K-292-452

PACKAGING: REEL (10K/REEL)

		DRAWN BY		V.K		14K SERIES PIN CONTACT, 2.50 PITCH							
		DRAWN DATE		02/20/24									
		CHECKED BY		R.S.M.									
		CHECK DATE		05/26/24		PART NUMBER		14K-292-421					
RoHS COMPLIANT	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC, AND SHALL NOT BE REPRODUCED , OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	TOLERANCES		ALL DIMENSIONS AND TOLERANCES IN MM		MATERIAL		PHOSPHOR BRONZE		SIZE		A	
		.X				±0.3		NOTES:				REVISION	
		.XX				±0.2						R2	
		.XXX				±0.1		SCALE		5:1		SHEET	