










PC MOUNTING

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
5-6	OPEN	5-4

CIRCUIT: SPDT
ON - OFF - ON

NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACTS/TERMINALS: GOLD PLATED OVER NICKEL PLATED
- RATING: 0.4 VA max. @ 20V AC or DC Max.
- CONTACT RESISTANCE: 100m OHM Max.
- ELECTRICAL LIFE: 6,000 CYCLES
- MECHANICAL LIFE: 40,000 CYCLES
- INSULATION RESISTANCE: 500M OHM min.
- DIELECTRIC STRENGTH: 500 V RMS @ SEA LEVEL
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- SEAL RATING: IP67



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-103941	Print update	02/26/26	MW					000024891
					TITLE 200USP3T1A1M7RE				
					SCALE 2:1	DATE 4/30/2013	DR EBP	DWG T250010	REV C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED