

BLACK BEZEL

BLACK ROCKER


PDS. 1 PDS. 2 PDS. 3

* DIMENSION IS 15.75/15.88 FOR PANEL THICKNESS BETWEEN 1.52mm TO 3.18mm

RECOMMENDED PANEL MOUNTING

PANEL THICKNESS

1.52 TO 3.18




NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4 X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 2 AMPS @ 250VAC 5 AMPS @ 120VAC OR 28VDC
5. CONTACT RESISTANCE: 10mILLI Ohms max initial @2-4VDC, 100mA for AG & AU
6. ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sea level
9. OPERATING TEMP.: -30°C to 85°C

CIRCUIT: 4PDT CONTACT CONFIGURATION

SWITCH FUNCTION			
PDS. 1	PDS. 2	PDS. 3	
DN	N/DNE	DN	
2-3, 5-6	DPEN	2-1, 5-4	8-7, 11-10

BOTTOM VIEW



E-SWITCH®

D	19948	CORRECT RATING	05/13/11	BMA	TITLE				
C	12202	REVISED AND REDRAWN	5/31/02	CB	300 4P-1 R6 BLK M1 Q E BLK				
REV.	ECN No.	DESCRIPTION	DATE	CHKD	SCALE	DATE	DR	DWG	REV
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					2:1	5/31/02	CB	T346003	D