





BLACK BEZEL

RECOMMENDED PANEL MOUNTING



PANEL THICKNESS

1.52 TO 3.18

* DIMENSION IS 15.75/15.88
FOR PANEL THICKNESS BETWEEN
1.52mm TO 3.18mm



CIRCUIT: DPDT



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC OR 28VDC
2A @250VAC
5. MATERIAL: FIXED TERMINAL & MOVING CONTACT
Copper Alloy w/Silver Plate
6. CONTACT RESISTANCE: 10milli Ohms max initial
@2-4VDC, 100mA for AG & AU
7. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
8. INSULATION RESISTANCE: 1,000M ohm min.
9. DIELECTRIC STRENGTH: 1000V RMS @sea level
10. OPERATING TEMP.: -30°C to 85°C

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
DN	DPFF	DN
2-3,5-6	DPEN	2-1,5-4

REVISED 4 DIMENSIONS			E-SWITCH		
C	18370	REVISED DESC./ PER CATALOG	12/31/08	BLR	TITLE
B	12120	RELEASED FOR PRODUCTION	5/6/02	CB	300 DP-3 R6 BLK M1 Q E BLK
A	10538	DESCRIPTION	2/17/00	MM	SCALE
REV.	ECN No.	DATE	CHKD	DATE	DR
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			2:1	2/17/00	MM
				DWG	T3223002
				REV	C