




SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3	1-2

(ON) = MOMENTARY



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: GOLD
5. CONTACT RESISTANCE: 20 mΩ MAX.
6. RATING: 0.4 A @ 20V (AC or DC)
7. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
8. MECHANICAL LIFE: 50,000 CYCLES
9. INSULATION RESISTANCE: 1,000 MΩ MIN.
10. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
11. INGRESS PROTECTION: IP67
12. OPERATING TEMP.: -40°C to 85°C
13. ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-103090	700A SERIES UPDATE	11/25/24	JS



OBJECT ID
000025809

TITLE 700ASP7B10M2RE				
SCALE 2:1	DATE 5/24/2010	DR BLR	DWG T750013	REV B