








NOTE:

1. ALL DIMENSIONS IN MM [INCH].
2. GENERAL TOLERANCE:  $X.X \pm 0.4$   
 $X.XX \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 0.3A @ 125VAC
6. CONTACT RATING: (NON-SWITCHING) 5A
7. OPERATING FORCE 800  $\pm$  300gm-cm
8. OPERATING TEMP: -30°C to 85°C
- ▲ 9. CIRCUIT SP: 4 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:  
LOCKWASHER, HEXNUT, STOP RING
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2011/65/EU (ROHS) COMPLIANT

|                                                                                                                 |        |                         |         |    |                                                                                                        |                          |                 |                       |                 |
|-----------------------------------------------------------------------------------------------------------------|--------|-------------------------|---------|----|--------------------------------------------------------------------------------------------------------|--------------------------|-----------------|-----------------------|-----------------|
| C                                                                                                               | 23292  | update print            | 4/2/18  | MW |  <b>E-SWITCH®</b> |                          |                 |                       |                 |
| B                                                                                                               | 22851  | update drawing          | 5/16/17 | MW |                                                                                                        |                          |                 |                       |                 |
| A                                                                                                               | 17486  | RELEASED FOR PRODUCTION | 7/26/07 | BF | <b>TITLE KC14A9.501NPS</b>                                                                             |                          |                 |                       |                 |
| REV                                                                                                             | PCR NO | DESCRIPTION             | DATE    | BY |                                                                                                        |                          |                 |                       |                 |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY<br>TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |        |                         |         |    | <b>SCALE</b><br>2:1                                                                                    | <b>DATE</b><br>7/26/2007 | <b>DR</b><br>BF | <b>DWG</b><br>G510363 | <b>REV</b><br>C |