







RECOMMENDED PANEL MOUNTING

a—(L)—b (+)
CIRCUIT



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. OPERATING TEMP: -25°C to +55°C
5. STORAGE TEMP: -40°C TO +85°C
- ▲ 6. LAMP VOLTAGE: 6V AC/DC 200mA (Incandescent Bulb)
7. SEAL: PROTECTED TO IP40.
8. PANEL THICKNESS: 0.5 - 5.0 mm
9. PACKAGE: 20 PER BOX
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT.

PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040003	L16PL10 BODY
2	1	F050104	50-001-04 RED CONCAVE TRANSPARENT LENS
3	1	F050402	50-004-02 6V AC/DC 200mA (Incandescent Bulb)



A	22486	RELEASED FOR PRODUCTION	9/8/16	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE L16PLR10ARED

SCALE 3:2	DATE 9/8/2016	DR MW	DWG XF0909P	REV A
--------------	------------------	----------	----------------	----------