








RECOMMENDED PANEL MOUNTING



PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040001	L16PLT10
2	1	F050204	50-002-04 RECTANGULAR CONCAVE GREEN RED
3	1	F050420	50-004-20 12V RED LED

a — (L) — b(+)
 CIRCUIT



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. OPERATING TEMP: -25°C to +55°C
5. STORAGE TEMP: -40°C TO +85°C
- ▲ 6. LAMP VOLTAGE: 12VDC RED LED
7. ▲ DENOTES CRITICAL PARAMETER.
8. PANEL THICKNESS: 0.5 - 5.0 MM
- 9 SEAL RATING: IP 40
10. 2002/95/EC (ROHS) COMPLIANT



A	18382	RELEASED FOR PRODUCTION	1/19/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE L16PLT10JREDRED

SCALE 1.5:1

DATE 1/19/2009

DR BLR

DWG XF0780P

REV A