





RECOMMEND PANEL MOUNTING  
(MAX. PANEL THK. 4mm)



Parts List			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F060610	LASOAU11 (MOMENTARY)
2	1	F051701	29MM RING FOR LA SERIES
3	1	F060291	29MM BLUE LENS
4	1	F060250	29MM LA U1 NUT



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
  2. GENERAL TOLERANCE: X.X = ±0.4  
X.XX = ±0.25
  3. TERMINAL NUMBERS FOR REF ONLY
  4. RATING: 5A @ 250VAC, 8A @ 125VAC  
0.2A @ 250VDC, 6A @ 24VDC
  5. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
  6. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
  7. OPERATING TEMP.: -25°C to 70°C
  - ▲ 8. LAMP VOLTAGE: NO LAMP
  - ▲ 9. ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-101457	print update	12/16/22	MW



OBJECT ID  
000027768

TITLE LASOAU110BLU				
SCALE 3:2	DATE 6/25/2003	DR AR	DWG XF0559P	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED