




## NOTES:



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA  
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100 Mega-OHM. MIN.
7. OPERATING FORCE: 250  $\pm$  100 GRAMS
8. OPERATING TEMP.: -40°C to 85°C
- ▲ 9. TRAVEL: MOMENTARY  
1.80  $\pm$  0.3mm FULL TRAVEL
10. CONTACT RESISTANCE: 50 Milli-OHM. MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LED: NONE



▲ ACTUATOR  
COLOR: RED

▲ HOUSING  
COLOR: BLACK

EPOXY  
SEAL



E-SWITCH®

|     |        |             |         |    |
|-----|--------|-------------|---------|----|
| A   | 24758  | RELEASE     | 2/25/21 | MW |
| REV | PCR NO | DESCRIPTION | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP40A1PBARN

SCALE

2:1

DATE

2/24/2021

DR

MW

DWG

B240061

REV

A