






NO ACTUATOR CAP



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA  
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100M $\Omega$ . MIN.
7. OPERATING FORCE: 250gf  $\pm$  100 GRAMS
8. OPERATING TEMP.: -40°C to 85°C
- ▲ 9. TRAVEL: 1.80  $\pm$  0.3mm FULL TRAVEL, MOMENTARY
10. CONTACT RESISTANCE: 50 m $\Omega$ . MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2011/65/EU (ROHS) COMPLIANT
- ▲ 13. LED COLOR: RED

| LED SPECS          | UNITS | RED     |
|--------------------|-------|---------|
| FORWARD CURRENT    | mA    | 20      |
| FORWARD VOLTAGE    | V     | 1.9-2.5 |
| LUMINOUS INTENSITY | MCD   | 200     |



E-SWITCH®

TITLE LP40A1PBNNR

SCALE  
2:1DATE  
3/20/2017DR  
MWDWG  
B240059REV  
A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|     |        |                        |         |    |
|-----|--------|------------------------|---------|----|
| A   | 22769  | RELEASE FOR PRODUCTION | 3/20/17 | MW |
| REV | PCR NO | DESCRIPTION            | DATE    | BY |