



- NOTES:**
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
 3. TERM. NUMBERS FOR REFERENCE ONLY.
 4. RATING: 12VDC, 12mA; SPST
 5. CONTACT MATERIAL: GOLD
 6. CONTACT RESISTANCE: 50 mΩ MAX.
 7. INSULATION RESISTANCE: 500VDC, 100 MΩ MIN.
 - ▲ 8. OPERATING FORCE: 150 ± 100gf
 9. OPERATING LIFE: 200,000 CYCLES
 10. OPERATING TEMP: -40°C to +85°C
 - ▲ 11. LED COLORS: GREEN / WHITE
 12. TRAVEL: 2.20mm ±0.20mm
 13. ▲ DENOTES CRITICAL PARAMETER.

▲ LED SPECS	UNITS	GREEN	WHITE
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE @20mA	VDC	1.6-2.5	2.8-4.0
LUMINOUS INTENSITY @20mA	mcd	20-80	120-400



B	24793	updated notes and LED specs	3/9/21	MW
A	24751	RELEASE	2/23/21	MW
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE LP60A1ASGW				
SCALE	DATE	DR	DWG	REV
2:1	2/23/2021	MW	B220016	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED