




PANEL THICKNESS	X
0.75-1.25	19.2
1.25-2.00	19.4
2.00-3.00	19.8



RECOMMENDED PANEL CUT-OUT



▲ SCHEMATIC
SPST
OFF - ON

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X ± 0.4
X.XX ± 0.25
3. ELECTRICAL LIFE: 6,000 [cURus]
4. CONTACT RESISTANCE: 20 m Ω MAX. INITIAL
5. INSULATION RESISTANCE: 100 M Ω AT 500VDC
6. OPERATING TEMPERATURE: -20°C to +65°C [cURus]
7. CONTACT RATING: 16A, 125VAC-250VAC, [cURus]
8. DIELECTRIC STRENGTH: 1000V FOR 1 MINUTE
9. TERMINALS TO BE SILVER PLATED
10. ▲ DENOTES CRITICAL PARAMETER



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100492	REMOVE VDE FROM NOTES	12/14/21	JS	TITLE PA411C9900				000000194
					SCALE	DATE	DR	DWG	REV
					3:2	11/2/2017	MW	14-PA411C9900	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED