






RECOMMENDED PANEL CUTOUT  
MAX. PANEL THICKNESS  
11.0 [.43 in]



▲ SWITCH FUNCTION

| POS. 1            | POS. 2                |
|-------------------|-----------------------|
|                   |                       |
| 1-2 ON<br>3-4 OFF | 1-2 (OFF)<br>3-4 (ON) |

( ) = MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4  
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -40°C TO 85°C
11. TRAVEL: 2.8 [.11 in]
12. ▲ DENOTES CRITICAL PARAMETER
13. LAMP VOLTAGE: 12V
14. INGRESS PROTECTION: IP65
15. HARDWARE SUPPLIED: O-RING AND HEXNUT

| REV | ECO NO     | DESCRIPTION       | DATE     | BY | E-SWITCH®           |           |     |                 | OBJECT ID |
|-----|------------|-------------------|----------|----|---------------------|-----------|-----|-----------------|-----------|
| C   | ECO-103877 | PV4 SERIES UPDATE | 01/13/26 | MR | TITLE PV4F2Y011-314 |           |     |                 | 000002676 |
|     |            |                   |          |    | SCALE               | DATE      | DR  | DWG             | REV       |
|     |            |                   |          |    | 1:1                 | 11/1/2010 | CAB | 52-PV4F2Y011314 | C         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED