

RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS
11.0 [.43 in]

Ø22.00
[.866 in]
Ø15.4
[Ø.61 in]
Ø12.0
[Ø.47 in]

▲ RING
ILLUMINATION COLOR:
RED / GREEN


▲ FLAT
ACTUATOR FINISH:
STAINLESS STEEL



▲ SWITCH FUNCTION

POS. 1	POS. 2
1-2 ON 3-4 OFF	1-2 (OFF) 3-4 (ON)

() = MOMENTARY




2.0
[.08 in]
▲ 34.6 ± 1.0
[1.36 ± .04 in]

▲ BODY FINISH:
STAINLESS STEEL

7.60
[.299 in]

9.60
[.378 in]
7.50
[.295 in]

M19 X 1.0



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 24VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 MΩ MIN.
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- OPERATING TEMP.: -40°C TO 85°C
- TRAVEL: 2.8 [.11 in]
- ▲ DENOTES CRITICAL PARAMETER
- LAMP VOLTAGE: 12V
- INGRESS PROTECTION: IP65
- HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
D	ECO-103878	PV4 SERIES UPDATE	01/15/26	MR	TITLE PV4F6Y0SS-3G4				000002735
					SCALE	DATE	DR	DWG	REV
					1:1	2/13/2017	MW	52-PV4F6Y0SS3G4	D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED