


PANEL MOUNTING
MAX. PANEL THICKNESS 4mm

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY





▲ CIRCUIT: SPST

▲ DOMED
ACTUATOR COLOR:
GREEN

▲ BODY COLOR:
STAINLESS STEEL

M12x1.0
THREAD



Ø17.50
[.689 in]

Ø12.60
[.496 in]

9.2±1.0
[.36±.04 in]

7.2±1.0
[.28±.04 in]

12.9±1.0
[.51±.04 in]



5.10
[.201 in]

4.20
[.165 in]

2.00
[.079 in]

NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- ▲ CONTACT MATERIAL: SILVER
- RATING: 2A @ 36 VDC
- ELECTRICAL LIFE: 200,000 CYCLES
- CONTACT RESISTANCE: 50 mΩ MAX. @ 1A 12VDC (INITIAL)
- INSULATION RESISTANCE: 1,000 MΩ MIN. @ 500VDC.
- DIELECTRIC STRENGTH: 2,000 VAC rms.
- OPERATING TEMPERATURE: -40°C TO +85°C.
- PANEL THICKNESS MAX: 4.0 mm.
- INGRESS PROTECTION: IP65
- ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. HARDWARE INCLUDED, 1 O-RING & 1 HEX NUT.(NOT SHOWN)

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-103847	PRINT UPDATE	01/06/26	JS	TITLE PV5S240S8				000002804
					SCALE	DATE	DR	DWG	REV
					2:1	4/15/2014	EBP	52-PV5S240S8	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED